



Equipment Shelves, Cantilevered

Content: Stationary 16ga shelf, #12-24 mounting hardware

Type	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Load Capacity	Catalog. No.
Solid	3.5" (89)	17" (432)	14" (356)	50lb	MCCCS19
Perforated	3.5" (89)	17" (432)	14" (356)	50lb	MCCCS19P
Solid	7.0" (178)	19" (483)	20" (508)	200lb	MCCCWS19HD



MCCCS19



MCCCWS19HD



MCCCWS19

Equipment Shelves, Center-Weighted

Content: Stationary 16ga shelf, #12-24 mounting hardware

Type	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Load Capacity	Catalog. No.
Solid	3.5" (89)	17" (432)	19" (483)	75lb	MCCCWS19

Horizontal Grounding Bar for 19" Rack

Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Hole1 Qty	Hole1 Size	Hole2 Qty	Hole2 Size	Catalog No.
.25" (6)	.75" (19)	19" (483)	8	#6-32	4	0.25" (6)	HBBBHR19

Horizontal Grounding Bar for 19" Rack

Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Hole1 Qty	Hole1 Size	Hole2 Qty	Hole2 Size	Catalog No.
.25" (6)	5/8 (16)	36" (914)	16	1/4-20	3	.25 (6) x .5 (12) Slot	HBBBVR36

Caster Kit

Catalog. No.

H2KMB



Network Cabinet Fan Kit, 460 CFM

Enclosure will accept 2 Fan Kits

Catalog. No.

H2KNF



Vertical Cable Management Bar

Size	Catalog. No.
for 80" cabinet	H280CM
for 84" cabinet	H284CM

