



- 110 Style Audio/Video Modules
- Quick and Easy 110 Termination
- Provides Composite, Component and S-Video Transmissions



Specifications

- Connector:
 - Connector body: brass
 - Plating: nickel 100μ"
 - Contact: nickel over phosphorous bronze
- Material:
 - Module: flame-retardant polymer UL 94V-0



110 Audio Video Modules, 1.5 Unit

RCA component Video, L/R Audio, 110 Termination, 75 ft. max., Category 3, 5, 5e, 6, 6A UTP

RCA component Video, 3.5mm Audio, 110 Termination, 75 ft. max., Category 3, 5, 5e, 6, 6A UTP

RCA Composite Video, 3.5mm Audio, 110 Termination, 75 ft. max., Category 3, 5, 5e, 6, 6A UTP

RCA component Video with S-video, 110 Termination, 75 ft. max., Category 3, 5, 5e, 6, 6A UTP

IMCAR11015xx

IMC3511015xx

IMR3511015xx

IMSC11015xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White).
Light Almond is the same color as Office White. See color chart on page V30.



110 Audio Video Modules, 1 Unit

RCA component Video to 110 Termination, 1 Unit, 75 ft. max. High Definition, Category 3, 5, 5e, 6A UTP

S-video, with Left/Right RCA Audio to 110 Termination, 1 Unit, 100' max. Category 3, 5, 5e, 6A UTP

S-video, 3.5mm Stereo Audio Jack to 110 Termination, 1 Unit, 100' max. Category 3, 5, 5e, 6A UTP

RCA Composite Video with Left/Right Audio to 110 Termination, 1 Unit, 100' max. Category 3, 5, 5e, 6A UTP

RCA Left/Right Audio 110 Termination, 1 Unit, 100' max. Category 3, 5, 5e, 6A UTP

IMCR1101xx

IMSR1101xx

IMSV351101xx

IMR1101xx

IMAR1101xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White).
Light Almond is the same color as Office White. See color chart on page V30.