

SC Field Terminating, single mode, 900 micron buffer, 25 pack

OR-205KAS9FB-09



Discontinued SC Field Terminating, single mode, 900 micron buffer, 25 pack. OptiMo field-installable SC connector for use with single mode fiber. The OptiMo technology incorporates a factory-bonded fiber stub, ceramic ferrule, and precise factory polish.

features & benefits

- Factory produced connector polish
- Factory polish process monitored using advanced laser interferometry
- No polishing required in the field
- No epoxy required
- Unlimited shelf life connector
- 62.5/125, Enhanced 50/125 and single mode options
- Lightweight, convenient Termination Kit

specifications

General Info

Typical Applications: Single-mode
Connection Type: SC
Product Series: OptiMo

Cord Information

Fiber Type: Single mode
Finish End One: Super Physical Contact-SPC
Max Return Loss: -40

Technical Information

Field Assembly Time: 1 minute on 900 micron buffer, 3 minutes on jacketed cable
Operating Temperature Fahrenheit: 32 to 131 degrees F (0 to + 55 degrees C)
Storage Temperature: -40 to + 104 degrees F (-40 to + 40 degrees C)

Typical Insertion Loss: 0.30000001

Typical Return Loss: -50

Equipment Type: Pre-polished Connectors