

LC PC reusable connector, field- installable, 50/125 LOMF

OR-205KNT9GA-50T



LC PC reusable connector, field-installable,
50/125 LOMF, aqua housing, white 900
micron boot

features & benefits

- **No epoxy or polishing:** Fast, easy assembly in the field
- **Reusable termination capability:** Saves time and money; reduces scrap
- **VFL window:** Immediate feedback on successful termination
- **Factory prepared and verified endface:** Reliability and superior performance
- **No special tools required:** Common fiber tools, readily available

specifications

General Info

Category Performance Application: OM3
Color: Aqua
Typical Applications: Multimode
Connection Type: LC
Product Series: Infinium

Cord Information

Connector Type End One: LC PC
Connector Type End Two: LC PC
Fiber Type: Multimode
Finish End One: Physical Contact-PC
Finish End Two: Physical Contact-PC
Max Insertion Loss: 0.3 dB
Max Return Loss: 22 dB

Technical Information

Connector Intermateability End One: IEC 61754-4

Connector Intermateability End Two: IEC 61754-4

Equipment Type: Pre-polished Connectors