

48-port voice/data panel, standard density, mod to 110, 19" x 5.25"

OR-809004910



Modular Quad Frame to 110 Patch Panel, 48 ports, active positions 2, 3, 4 and 5 of six-position RJ14 jack.

features & benefits

- Standard density design
- 110 termination

specifications

General Info

Mod Jack Wiring: RJ14 (2,3,4,5)
Number Of Ports: 48

Listing Agencies/Third Party Information

CSA Listing Info: LR 90894
CUL Listing No: E131600
FCC Standard: Yes
UL Listing No: E131600
UL Standard: Yes

Construction Information

Component1: Panel
Component2: Six-position jack housing
Component3: Modular jack contacts
Component4: 110 rear bracket
Component5: 25-pair base strip
Finish Plating1: Painted black - texture, with white silkscreen

Finish Plating3: 50 micro inch gold or GTX
Finish Plating4: Painted black - no texture
Material1: 0.125" Aluminum
Material2: ABS UL94V-0
Material3: Phosphor Bronze
Material4: 0.063" Aluminum
Material5: Polycarbonate UL94V-0

Dimensions

Cable Diameter Range: 22-26 AWG
Depth Metric: 3.175 mm
Height Metric: 133.35 mm
Height U S: 5.25 in
Width Metric: 482.6 mm

Technical Information

Performance Rating: Voice/Data