

1U rack mount fiber cabinet for combination patch/splice applications

OR-FC01U-C



1U rack mount fiber cabinet for combination patch/splice applications

features & benefits



- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

specifications

General Info

Installation Destination: Rack Mount
Product Series: OptiMo FC Series

Dimensions

Depth Metric: 485.77 mm
Height Metric: 44.45 mm
Height U S: 1.75"
Width Metric: 482.60 mm
Rack Units: 1

Technical Information

Capacity: Standard density
Equipment Type: Fiber Cabinets

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant