

2U rack mount fiber cabinet for patching applications

OR-FC02U-P



The 2U (3.50" high) fiber cabinet for patching applications is optimized for integration with the Mighty Mo 6 rack system (OR-MM6710, OR-MM6810 & Seismic Rack OR-MM6710S) with 10.5" channel depth. Each fiber cabinet accepts up to six adapter panels, six Momentum 1U cassettes or three Momentum 2U cassettes.



features & benefits

- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

specifications

General Info

Installation Destination: Rack Mount
Product Series: OptiMo FC Series

Dimensions

Depth Metric: 485.77 mm
Height Metric: 88.90 mm
Height U S: 3.5"
Width Metric: 482.60 mm
Rack Units: 2

Technical Information

Capacity: Standard density
Equipment Type: Fiber Cabinets

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant