

## 4U rack mount fiber cabinet for patching applications

OR-FC04U-P



4U rack mount fiber cabinet for patching applications

### features & benefits



- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

### specifications

#### General Info

Installation Destination: Rack Mount  
Product Series: OptiMo FC Series

#### Dimensions

Depth Metric: 485.77 mm  
Height Metric: 177.80 mm  
Height U S: 7"  
Width Metric: 482.60 mm  
Rack Units: 4

#### Technical Information

Capacity: Standard density  
Equipment Type: Fiber Cabinets

## **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant