

Infinium High Density MPO-to-LC Cassette, OS2

OR-HDCA6LC12AJ



Spanning 6 positions in the HD patch panel, the MTP-to-LC 12-fiber cassette is available with 50-micron laser optimized (OM4+) fiber or with singlemode (OS2) fiber.

features & benefits

- **High Density:** Optimize space utilization
- **Sliding Lock:** Quick and easy installation

specifications

General Info

Available Internationally: Yes
Category Performance Application: OS2
Number Of Ports: 12
Typical Applications: Single-mode
Installation Destination: HD Patch Panel
Product Series: Infinium

Assembly/Installation Information

Mounting Hardware Included: Yes

Dimensions

Rack Units: 0.5

Cord Information

Connector Type End One: MTP-LC
Connector Type End Two: MTP-LC
Fiber Type: Single-mode
Finish End One: Ultra Physical Contact - UPC
Finish End Two: Ultra Physical Contact - UPC
Max Insertion Loss: 1.05 dB
Max Return Loss: < - 55 dB

Technical Information

Connector Intermateability End One: TIA/EIA-604-12
Connector Intermateability End Two: TIA/EIA-604-12
Fiber Capacity: 12
Capacity: High Density
Equipment Type: Pre-Terminated Cassettes