

# Keystone Recessed F-conn 75 Ohm Electrical Ivory

**OR-KSFCNR-13** 



Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.

## features & benefits

Recessed design: Provides a more flush aesthetic look.

**Low profile connector:** Allows furniture to be placed closer to the wall. **Designed for multiple coax cable styles:** Accepts both push-style and screw-style.

**75 Ohm F-connector:** Ideal for cable/satellite TV, cable modems, and security cameras.

**TechChoice keystone footprint:** Fits in all TechChoice faceplates and housings.

**Rear loading module:** Allows for termination before and during the construction process.

**Integrates with Legrand | Wiremold :** Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

### specifications

#### **General Info**

Footprint: Keystone Number Of Ports: 1

Termination: Female to Female Coupler

Typical Applications: Cable TV(CATV), closed circuit TV (CCTV), satellite TV, security cameras, cable modems

Product Series: Keystone

Type: Video

#### **Listing Agencies/Third Party Information**

CUL Listing No: E131600 UL Listing No: E131600

#### **Construction Information**

Component1: Plastic TechChoice Keystone Housing Material1: High Impact Thermoplastic ABS 94V-0

#### **Dimensions**

Depth Metric: 22.23 mm Depth U S: 0.875"

#### **Technical Information**

Connection Method: Accepts push-on or screw-on style coax cables

Ohm Value: 75 Ohm
Performance Rating: 3GHz
Equipment Type: F-connector