

Keystone Recessed F-conn 75 Ohm Wiremold Ivory

OR-KSFCNR-99



Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.

features & benefits

Recessed design: Provides a more flush aesthetic look.

Low profile connector: Allows furniture to be placed closer to the wall.

Designed for multiple coax cable styles: Accepts both push-style and screw-style.

75 Ohm F-connector: Ideal for cable/satellite TV, cable modems, and security cameras.

TechChoice keystone footprint: Fits in all TechChoice faceplates and housings.

Rear loading module: Allows for termination before and during the construction process.

Integrates with Legrand | Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

specifications

General Info

Footprint: Keystone

Number Of Ports: 1

Termination: Female to Female Coupler

Typical Applications: Cable TV(CATV), closed circuit TV (CCTV), satellite TV, security cameras, cable modems

Product Series: Keystone

Type: Video

Listing Agencies/Third Party Information

CUL Listing No: E131600

UL Listing No: E131600

Construction Information

Component1: Plastic TechChoice Keystone Housing
Material1: High Impact Thermoplastic ABS 94V-0

Dimensions

Depth Metric: 22.23 mm
Depth U S: 0.875"

Technical Information

Connection Method: Accepts push-on or screw-on style coax cables
Ohm Value: 75 Ohm
Performance Rating: 3GHz
Equipment Type: F-connector