

# MM20 Lightweight Airflow Baffles, for MM20830 rack and MM20VMD812 vertical manager

OR-MM20ABL83012-X



Mighty Mo 20 airflow baffles mount between racks, direct intake and exhaust air on side flow network equipment from cold aisle to hot aisle. The patented angle design utilizes less space, reduces back pressure and provides better overall performance than square duct style systems.

Note: Replace the "X" tail code with "B" for black or "W" for white.



## features & benefits

- **Full height angled design:** Provides increased intake area over square duct designs and reduces back pressure on the exhaust side of the switch.
- **Manufactured from recycled PVC/ABS resin:** Chemical and corrosion resistant, low flammability (UL-94 VO flame rating), perfect for data center use.
- **Lightweight foam core construction:** Much easier to install, thermal and sound insulation (absorbs vibrations and oscillations) and reduced shipping cost and possibility of damage

## specifications

**General Info**

Color: (B)lack or (W)hite  
Product Series: Mighty Mo 20  
Type: Rack Accessories  
Component Type: Airflow Baffle

**Construction Information**

Component1: Airflow Baffle

**Dimensions**

Diameter Metric:  
Length Metric:

**Technical Information**

Patent No: 8,130,494 and 8,256,181

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant