

MM20 Vertical Manager with Door, 6.5"W x 10.25"D for 8' MM20 racks

OR-MM20VMD806-X



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged slam latch doors allow easy access during moves, adds and changes. Supplied with four cable management spools to provide slack storage for fiber jumpers and twelve bend limiting clips to protect fiber entering the vertical manager.

Note: Replace the "X" tail code with "B" for black or "W" for white.



features & benefits

- **Vertical cage with individual rack unit fingers:** Provides organized method for routing and storage of patch or cross connect cable between racks.
- **Recommended fill capacity of up to 350 Category 6 patch cords at 40% fill:** See patch cord capacity data sheet for full chart.
- **Slam latch hinged extruded aluminum front door:** Full length handle allows easy access during moves, adds and changes and slams shut.
- **Mounted on the front flange between the Mighty Mo 20 racks when two or more are installed in a row:** Creates a channel between racks for front to back routing of equipment cables and patch cords.
- **Supplied with four slack storage spools and 12 bend limiting clips:** Adjustable bend limiting control for copper and fiber cords.
- **All necessary mounting hardware included:** Hanger clips hold the cage in place for easy and quick one person installation.

specifications

General Info

Color: (B)lack or (W)hite
Product Series: Mighty Mo 20
Type: Vertical Managers
Component Type: Vertical Manager with Door

Assembly/Installation Information

Mounting Hardware Included: Yes

Construction Information

Component1:

Dimensions

Depth U S: 10.25
Diameter Metric:
Height Metric: 2.2606 m
Height U S: 89"
Length Metric:
Width Metric: 165.1 mm
Width U S: 6.5"
Height: 89"

Technical Information

Patent No: 6,946,605 and 7,026,553

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant