

## MM20 Vertical Manager with Cover, 6"W x 8.62"D for 7' MM20 racks

OR-MM20VMS706-X



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged snap-on covers allow easy access during moves, adds and changes. A 6" wide cage is supplied with four cable management spools and 12 bend-limiting clips.

Note: Replace the "X" tail code with "B" for black or "W" for white.



### features & benefits

- **Vertical cage with individual rack unit fingers:** Provides organized method for routing and storage of patch or cross connect cable between racks.
- **Recommended fill capacity of up to 350 Category 6 patch cords at 40% fill:** See patch cord capacity data sheet for full chart.
- **Dual snap on hinged covers:** The door allows easy access during moves, adds and changes.
- **Mounted on the front flange between the Mighty Mo 6 racks when two or more are installed in a row, on a single rack or the end of a row:** 6" and 10" widths create a channel between racks for front to back routing of equipment cables and patch cords.
- **6" and wider are supplied with four slack storage spools and 12 bend limiting clips:** Improved bend limiting control for copper and fiber cords.
- **All necessary mounting hardware included:** Hanger clips hold the cage in place for easy and quick one person installation.

### specifications

#### General Info

Color: (B)lack or (W)hite  
Product Series: Mighty Mo 20  
Type: Vertical Managers  
Component Type: Vertical Manager with Cover

### **Assembly/Installation Information**

Mounting Hardware Included: Yes

### **Construction Information**

Component1:

### **Dimensions**

Depth U S: 8.62

Diameter Metric:

Height Metric: 1.96215 m

Height U S: 77.25"

Length Metric:

Width Metric: 152.4 mm

Width U S: 6"

Height: 77.25"

### **Technical Information**

Patent No: 6,946,605 and 7,026,553

### **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Buy American Act Compliant