


single mode Pigtail, 6-fiber, 900 μ m, SC-UPC, 2 meters

OR-P1SC4ZRRZZZ002M



Ortronics has selected the best connectors in the industry for our fiber system components. Ortronics Fiber Assemblies can be ordered in various lengths and are available either in multimode or single mode fiber with any standard ceramic connector including ST, FC, LC & SC. For lengths, cable types, or connector styles not shown, please consult Ortronics sales at (800) 934-5432. When high density is required, Ortronics recommends the duplex MT-RJ and LC based products. Formally product number OR-626SC4ZR-RZ002M.

features & benefits

- **All common fiber types offered:** Provides industry leading performance and assures compliance to common industry standards.
- **Industry leading guarantee of 0.50 dB or better (versus TIA/EIA 568B.3 requirement of 0.75 dB):** Supports robust low loss fiber optic transmission in structured cabling systems.
- **100% visual inspection:** Ensures that all polished surfaces are free from defects.
- **100% Insertion Loss testing, test report included:** Ensures low loss connections.

specifications

General Info

Cable Type: Pigtails
Typical Applications: Single-mode

Dimensions

Length Metric: 2

Cord Information

Connector Type End One: SC-UPC
Connector Type End Two: Underminated
Finish End One: Ultra Physical Contact-UPC
Finish End Two: Physical Contact-PC
Jacket Rating: UL OFNR Riser
Max Insertion Loss: 0.40 dB
Max Return Loss: < - 55 dB
Min Bend Radius: 25 mm (1")

Technical Information

Fiber Capacity: 6
Performance Rating: Singlemode 9125
Equipment Type: Patch Cord