

# Rear load angled high density jack panel kit for 72 Clarity 6 or 5E panel jacks

OR-PHAPJU72



Rear load angled high density jack panel kit  
for 72 Clarity 6 or 5E panel jacks

## features & benefits



- Jacks rear load into panels
- New positive jack latching design
- Recessed design with lower mounted profile
- High density panel jack solution
- Panel jacks support snap-in icons
- Universal wiring labels on panel jacks
- Silkscreened 1-72

## specifications

### General Info

Color: Black with blue silkscreen  
Footprint: Clarity 6 or 5E rear load PJ series panel jacks  
Mod Jack Wiring: Field defined  
Number Of Ports: Up to 72  
Product Series: Clarity  
Type: Patch Panels

### Assembly/Installation Information

Installation Tips: Terminate panel jack and then rear load into the panel, maintaining minimum bend radius of four times the cable diameter.  
Mounting Hardware Included: Yes

### Listing Agencies/Third Party Information

CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

### **Construction Information**

Component1: Panel

Component2: Patch Panel Mounting Screws #12-24 x 5/8"

Finish Plating1: Black with blue silkscreen

Finish Plating2: Black

Material1: .090 aluminum

Material2: Steel

### **Dimensions**

Depth Metric: 38.86 mm

Height Metric: 88.90 mm

Height U S: 3.5"

Width Metric: 482.6 mm

### **Technical Information**

Category Rating: Cat6a

Performance Rating: Cat6a

### **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Buy American Act Compliant