

DOUBLE-BAY FRAMES
A-T-O

FEATURES

PROLINE™ offers the broadest range of standard sizes in the industry.

Standard Product

Catalog Number	AxBxC in./mm	Nominal Frame Size A x B x C	Maximum Subpanel Size mm/in.	Maximum Rack Mounting Space
PF7126	26.77 x 47.20 x 23.15 680 x 1199 x 588	700 x 1200 x 600	585 x 1130 23.03 x 44.49	13U x 2
PF16126	62.20 x 47.20 x 23.15 1580 x 1199 x 588	1600 x 1200 x 600	1485 x 1130 58.46 x 44.49	33U x 2
PF16128	62.20 x 47.20 x 31.02 1580 x 1199 x 788	1600 x 1200 x 800	1485 x 1130 58.46 x 44.49	33U x 2
PF18124	70.08 x 47.20 x 15.28 1780 x 1199 x 388	1800 x 1200 x 400	1685 x 1130 66.34 x 44.49	38U x 2
PF18125	70.08 x 47.20 x 19.21 1780 x 1199 x 488	1800 x 1200 x 500	1685 x 1130 66.34 x 44.49	38U x 2
PF18126	70.08 x 47.20 x 23.15 1780 x 1199 x 588	1800 x 1200 x 600	1685 x 1130 66.34 x 44.49	38U x 2
PF18128	70.08 x 47.20 x 31.02 1780 x 1199 x 788	1800 x 1200 x 800	1685 x 1130 66.34 x 44.49	38U x 2
PF18165	70.08 x 62.95 x 19.21 1780 x 1599 x 488	1800 x 1600 x 500	1685 x 1530 66.34 x 60.24	38U x 2
PF18166	70.08 x 62.95 x 23.15 1780 x 1599 x 588	1800 x 1600 x 600	1685 x 1530 66.34 x 60.24	38U x 2
PF18168	70.08 x 62.95 x 31.02 1780 x 1599 x 788	1800 x 1600 x 800	1685 x 1530 66.34 x 60.24	38U x 2
PF20124	77.95 x 47.20 x 15.28 1980 x 1199 x 388	2000 x 1200 x 400	1885 x 1130 74.21 x 44.49	42U x 2
PF20125	77.95 x 47.20 x 19.21 1980 x 1199 x 488	2000 x 1200 x 500	1885 x 1130 74.21 x 44.49	42U x 2
PF20126	77.95 x 47.20 x 23.15 1980 x 1199 x 588	2000 x 1200 x 600	1885 x 1130 74.21 x 44.49	42U x 2
PF20128	77.95 x 47.20 x 31.02 1980 x 1199 x 788	2000 x 1200 x 800	1885 x 1130 74.21 x 44.49	42U x 2
PF20165	77.95 x 62.95 x 19.21 1980 x 1599 x 488	2000 x 1600 x 500	1885 x 1530 74.21 x 60.24	42U x 2
PF20166	77.95 x 62.95 x 23.15 1980 x 1599 x 588	2000 x 1600 x 600	1885 x 1530 74.21 x 60.24	42U x 2
PF20168	77.95 x 62.95 x 31.02 1980 x 1599 x 788	2000 x 1600 x 800	1885 x 1530 74.21 x 60.24	42U x 2
PF22125	85.83 x 47.20 x 19.21 2180 x 1199 x 488	2200 x 1200 x 500	2085 x 1130 82.09 x 44.49	47U x 2
PF22126	85.83 x 47.20 x 23.15 2180 x 1199 x 588	2200 x 1200 x 600	2085 x 1130 82.09 x 44.49	47U x 2
PF22128	85.83 x 47.20 x 31.02 2180 x 1199 x 788	2200 x 1200 x 800	2085 x 1130 82.09 x 44.49	47U x 2

1 rack unit = 1.75 in. (44 mm)

SPECIFICATIONS

- Welded back centerpost
- No front centerpost for easy component installation
- Center top and bottom frame sections for internal component mounting
- Optional center uprights available to support mounting options
- Welded corners with steel corner blocks that add strength and rigidity
- 12 gauge, roll-formed frame sections for strength
- Flange on door and side openings deflects liquids away from the enclosure interior
- Rectangular frame holes are designed for metric cage nut fasteners
- Round frame holes allow numerous grounding locations using M5 thread-forming screws
- Access to both sides of frame mounting holes allows standard components to be easily installed
- Provisions for slide-in subpanel, rack mounting and accessory mounting
- Simple means for joining frames to create multiple-bay enclosures
- An open roll-formed profile design affords complete surface corrosion protection and assembly access
- Sealed mounting for all external accessories
- Finished with RAL 7035 textured light-gray polyester powder paint

BULLETIN: P20

