



107713554 | M12AS-270
Angled Specialty Faceplate, gray

General Specifications

Color	Gray
Mount Type	Flush
Product Type	Flush moun faceplate
Total Ports, quantity	2
Package Quantity	25

Dimensions

Depth	13.46 mm 0.53 in
Height	121.92 mm 4.80 in
Width	78.74 mm 3.10 in

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Safety Standard	UL
-----------------	----

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system