



760138586 | SLID-SHLF-550D-25KG-EMEA  
19 in (482.6 mm) x 21.6 in (550 mm) Sliding Shelf, 25 Kg Load Rating

## Dimensions

Depth	550.0 mm		21.7 in
Width	482.6 mm		19.0 in
Mounting Rail Depth, maximum	670.0 mm		26.4 in
Mounting Rail Depth, minimum	550.0 mm		21.7 in

## General Specifications

Ordering Note	Available in Europe, the Middle East, and Africa
Cabinet Type	Network cabinet   Server cabinet
Product Type	Shelf
Rack Units	1
Color	Black
Finish	Powder-coated, smooth
Package Quantity	1

## Mechanical Specifications

Material Type	Steel
Static Load Rating	25.0 kg   55.1 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

