



760138560 | HD-SHLF-650D-60KG-EMEA
19 in (482.6 mm) x 25.6 in (650 mm) Heavy Duty Shelf, 60 Kg Load Rating

Dimensions

Depth	650.0 mm		25.6 in
Width	482.6 mm		19.0 in
Mounting Rail Depth, minimum	650.0 mm		25.6 in

General Specifications

Ordering Note	Available in Europe, the Middle East, and Africa		
Cabinet Type	Network cabinet		Server cabinet
Product Type	Shelf		
Rack Units	2		
Color	Black		
Finish	Powder-coated, smooth		
Package Quantity	1		

Mechanical Specifications

Material Type	Steel		
Static Load Rating	60.0 kg		132.3 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

