



760138594 | HD-SLID-SHLF-567D-80KG-EMEA  
19 in (482.6 mm) x 22.3 in (567 mm) Heavy Duty Sliding Shelf, 80 Kg Load Rating

## Dimensions

Depth	567.0 mm		22.3 in
Width	482.6 mm		19.0 in
Mounting Rail Depth, maximum	605.0 mm		23.8 in
Mounting Rail Depth, minimum	567.0 mm		22.3 in

## General Specifications

Ordering Note	Available in Europe, the Middle East, and Africa
Cabinet Type	Network cabinet   Server cabinet
Product Type	Shelf
Color	Black
Finish	Powder-coated, smooth
Package Quantity	1

## Mechanical Specifications

Material Type	Steel
Static Load Rating	80.0 kg   176.4 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

