



**Broadband Solutions**  
**SVFAM3**  
**Inline Attenuator, 3 dB**



## Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	CE   EN 60728-4   SCTE

## Electrical Specifications

Operating Frequency Band	0 – 1002 MHz
Insertion Loss	3.00 dB
Frequency Response	±0.25 dB
Return Loss, input, minimum	25 dB
Return Loss, output, minimum	25 dB

## General Specifications

Device Type	Attenuator
Application	Reduces RF signal levels by a specific value
Brand	HomeConnect®

## Dimensions

Contact Pin Diameter	0.813 mm   0.032 in
Contact Pin Diameter Tolerance	±0.002 in

## Mechanical Specifications

Material Type	Brass
Plating	Nickel

## Packed Dimensions

Carton Quantity	2000
Height	241.30 mm   9.50 in
Length	342.90 mm   13.50 in
Width	241.30 mm   9.50 in
Shipping Weight	25.40 kg   56.00 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system