



Overview

AL168175CB Multi-Output Power Supply provides 16VAC distributed via eight (8) PTC protected outputs for powering multiple security system or access control panels.

Specifications

Input:

- Input 115VAC, 50/60Hz, 1.45 amp.

Output:

- Eight (8) PTC protected outputs.
- 16VAC output.
- 16VAC @ 10 amp (175VA) supply current (1.25 amp per device, 2.5 amp max.)
- Outputs are rated @ 2.5 amp.
- Main fuse rated @ 15 amp/32V.
- Surge suppression.

Visual Indicators:

- AC power LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.: 81.89 BTU/Hr.
- System AC input VA requirement: 166.75VA.

Features:

- Illuminated master power disconnect circuit breaker with manual reset.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 95.25mm)
- Product weight (approx.): 8.15 lbs. (3.7 kg).
- Shipping weight (approx.): 9.15 lbs. (4.15 kg).

Agency Approvals



European Conformity

Enclosure Dimensions (*H x W x D approximate*):
8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 95.25mm)

