

**Overview**

AL168600CB Multi-Output Power Supply provides 16VAC or 18VAC distributed via eight (8) PTC protected outputs for powering multiple security system or access control panels.

Specifications***Input:***

- Input 115VAC, 50/60Hz, 5.4 amp.

Output:

- Eight (8) PTC protected outputs.
- 16VAC or 18VAC output.
- 16VAC @ 40 amp (600VA) supply current (5 amp per device, 6 amp max.)
- or 18VAC @ 36 amp (600VA) supply current (4.5 amp per device, 6 amp max.).
- Outputs are rated @ 6 amp.
- Two (2) main fuse rated @ 15 amp/32V.
- Surge suppression.

Visual Indicators:

- AC power LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 16VAC: 327.57 BTU/Hr.
 - 18VAC: 331.66 BTU/Hr.
- System AC input VA requirement: 621VA.

Features:

- Illuminated master power disconnect circuit breaker with manual reset.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)
- Product weight (approx.): 24.9 lbs. (11.29 kg).
- Shipping weight (approx.): 26.1 lbs. (11.84 kg).

Agency Approvals

European Conformity

Enclosure Dimensions (H x W x D approximate):

13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)

