



Overview

AL168CB Multi-Output Power Supply provides 16VAC or 18VAC distributed via eight (8) PTC protected outputs for powering multiple security system or access control panels.

Specifications

Input:

- Input 115VAC, 50/60Hz, 0.9 amp.

Output:

- Eight (8) PTC protected outputs.
- 16VAC or 18VAC output.
- 16VAC @ 6 amp (100VA) supply current
(0.75 amp per device, 2.5 amp max.)
or 18VAC @ 5.5 amp (100VA) supply current
(0.6875 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Main fuse rated @ 10 amp/250V.
- Surge suppression.

Visual Indicators:

- AC power LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 16VAC: 49.13 BTU/Hr.
 - 18VAC: 50.67 BTU/Hr.
- System AC input VA requirement: 103.5VA.

Features:

- Illuminated master power disconnect circuit breaker with manual reset.

Mechanical:

- Enclosure Dimensions (H x W x D approx.):
8.5" x 7.5" x 3.5" (215.9mm x 190.5mm x 88.9mm).
- Product weight (approx.): 6.0 lbs. (2.72 kg).
- Shipping weight (approx.): 7.0 lbs. (3.175 kg).

Agency Approvals



European Conformity

Enclosure Dimensions (*H x W x D approximate*):
8.5" x 7.5" x 3.5" (215.9mm x 190.5mm x 88.9mm)

