



ALTV2416300ULCBM

Overview

ALTV2416300ULCBM provides 24VAC or 28VAC distributed via Sixteen (16) Class 2 Rated PTC protected power-limited outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications***Input:***

- 115VAC, 50/60Hz, 2.7 amp.

Output:

- Sixteen (16) Class 2 Rated PTC protected power-limited outputs.
- 24VAC @ 12.5 amp (300VA) supply current (0.781 amp per device, 2.5 amp max.) or 28VAC @ 10 amp (280VA) supply current (0.625 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 24VAC: 153.55 BTU/Hr.
 - 28VAC: 143.31 BTU/Hr.

Electrical (cont'd):

- System AC input VA requirement: 310.5VA.

Features:

- Secondary fuse rated @ 10 amp/250V.
- AC power LED.
- Power ON/OFF switch.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 97.9mm)
- Product weight (approx.): 8.2 lbs (3.7 kg)
- Shipping weight (approx.): 9.2 lbs (4.2 kg)

Agency Approvals

UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.



European Conformity

Enclosure Dimensions (H x W x D approximate):

8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 97.9mm)

