



ALTV2416600CB

Overview

ALTV2416600CB AC Wall Mount CCTV Power Supply provides 24VAC or 28VAC distributed via sixteen (16) PTC protected outputs for powering CCTV cameras, heaters and other video accessories.

Specifications***Input:***

- 115VAC, 50/60Hz, 5.4 amp.

Output:

- Sixteen (16) PTC protected outputs.
- 24VAC @ 28 amp (700VA) supply current (1.75 amp per device, 2.5 amp max.) or 28VAC @ 25 amp (700VA) supply current (1.563 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 24VAC: 343.94 BTU/Hr.
 - 28VAC: 358.26 BTU/Hr.

Electrical (cont'd):

- System AC input VA requirement: 621VA.

Features:

- Main fuse rated @ 15 amp/32V.
- AC power LED.
- Spare fuses provided.
(all models w/primary and/or secondary fuses).

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 13.5" x 13" x 3.25" (343mm x 330mm x 83mm).
- Product weight (approx.): 24.1 lbs (10.9 kg).
- Shipping weight (approx.): 25.1 Lbs (11.4 kg).

Agency Approvals

European Conformity

Enclosure Dimensions (H x W x D approximate):
 13.5" x 13" x 3.25" (343mm x 330mm x 83mm)

