



ALTV2432350CB

Overview

ALTV2432350CB AC Wall Mount CCTV Power Supply provides 24VAC or 28VAC distributed via thirty-two (32) PTC protected outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications***Input:***

- 115VAC, 50/60Hz, 2.7 amp.

Output:

- Thirty-two (32) PTC protected outputs.
- 24VAC @ 14 amp (350VA) supply current (0.438 amp per device, 2.5 amp max.) or 28VAC @ 12.5 amp (350VA) supply current (0.391 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 24VAC: 171.97 BTU/Hr.
 - 28VAC: 179.14 BTU/Hr.

Electrical (cont'd):

- System AC input VA requirement: 310.5VA.

Features:

- Secondary fuse rated @ 10 amp/250V.
- AC power LED.
- Power ON/OFF switch.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 13.5" x 13" x 3.25" (343mm x 330mm x 83mm).
- Product weight (approx.): 15.9 lbs (7.21 kg).
- Shipping weight (approx.): 16.9 lbs (7.67 kg).

Agency Approvals

European Conformity

Enclosure Dimensions (H x W x D approximate):
 13.5" x 13" x 3.25" (343mm x 330mm x 83mm)

