



ALTV248300CB

Overview

ALTV248300CB AC Wall Mount CCTV Power Supply provides 24VAC or 28VAC distributed via eight (8) PTC protected outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications***Input:***

- 115VAC, 50/60Hz, 2.7 amp.

Output:

- Eight (8) PTC protected outputs.
- 24VAC @ 14 amp (350VA) supply current (1.75 amp per device, 2.5 amp max.) or 28VAC @ 12.5 amp (350VA) supply current (1.563 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 24VAC: 171.97 BTU/Hr.
 - 28VAC: 179.13 BTU/Hr.

Electrical (cont'd):

- System AC input VA requirement: 310.5VA.

Features:

- Secondary fuse rated @ 15 amp/32V.
- AC power LED.
- Power ON/OFF switch.
- Spare fuses provided.
(all models w/primary and/or secondary fuses).

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 12.25" x 7.25" x 4.5" (311mm x 184mm x 114mm).
- Product weight (approx.): 11.4 lbs. (5.2 kg).
- Shipping weight (approx.): 12.4 lbs. (5.6 kg).

Agency Approvals

Enclosure Dimensions (H x W x D approximate):
12.25" x 7.25" x 4.5" (311mm x 184mm x 114mm)

