



ALTV615DC416ULCB **UL Listed DC CCTV Power Supply**

Rev. DSALTV615DC416ULCB - 10222012



ALTV615DC416ULCB

Overview

ALTV615DC416ULCB provide 6VDC to 15VDC distributed via sixteen (16) Class 2 Rated PTC protected power-limited outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications

Input:

- Input 115VAC, 50/60 Hz, 0.9 amp.

Output:

- Sixteen (16) Class 2 Rated PTC protected power-limited outputs.
- 6VDC to 15VDC field adjustable.
- 4 amp total continuous supply current (0.25 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Filtered and electronically regulated outputs.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 9-23 BTU/Hr.
- System AC input VA requirement: 103.5VA.

Features:

- AC input and DC output LED indicators.
- Illuminated power disconnect circuit breaker with manual reset.
- Unit maintains camera synchronization.
- Ease of installation saves time and eliminates costly labor.

Mechanical:

- NEMA1 enclosure.
- Enclosure Dimensions (H x W x D approx.): 13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)
- Product weight (approx.): 10.5 lbs. (4.76 kg).
- Shipping weight (approx.): 11.0 lbs. (4.99 kg).

Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

Enclosure Dimensions (H x W x D approximate):

13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)

