



ALTV615DC48ULCBM **UL Listed DC CCTV Power Supply**

Rev. DSALTV615DC48ULCBM - 10222012



ALTV615DC48ULCBM

Overview

ALTV615DC48ULCBM provides 6VDC to 15VDC distributed via eight (8) Class 2 Rated PTC protected power-limited outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications

Input:

- Input 115VAC, 50/60 Hz, 0.9 amp.

Output:

- Eight (8) Class 2 Rated PTC protected power limited outputs.
- 6VDC to 15VDC field adjustable.
- 4 amp total continuous supply current (0.5 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Filtered and electronically regulated outputs.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 12.28-30.71BTU/Hr.
- System AC input VA requirement: 103.5VA.

Features:

- AC input and DC output LED indicators.
- Power ON/OFF switch.
- Unit maintains camera synchronization.
- Ease of installation saves time and eliminates costly labor.

Mechanical:

- NEMA1 enclosure.
- Enclosure Dimensions (H x W x D approx.): 8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 95.25mm)
- Product weight (approx.): 8.65 lbs. (3.92 kg).
- Shipping weight (approx.): 9.15 lbs. (4.15 kg).

Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

Enclosure Dimensions (*H x W x D approximate*):
8.5" x 7.5" x 3.75" (215.9mm x 190.5mm x 95.25mm)

