



R615DC416ULCB **DC Rack Mount CCTV Power Supply**

Rev. R615DC416ULCB_10202014



R615DC416ULCB

Overview

R615DC416ULCB provides 6-15VDC distributed via sixteen (16) PTC protected outputs for powering CCTV cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 0.9 amp.

Output:

- Sixteen (16) Class 2 Rated PTC protected outputs.
- 6-15VDC @ 4 amp total output current.
(0.25 amp per device, 2.5 amp max.)
- Outputs are rated @ 2.5 amp.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 12.28 - 30.71 BTU/Hr.
- System AC input VA requirement: 103.5VA.

Features:

- Sixteen (16) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.

Mechanical:

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.):
3.26" x 19.125" x 8.5" (83mm x 486mm x 216mm)
- Product weight (approx.): 13.75 lbs. (6.24 kg).
- Shipping weight (approx.): 14.75 lbs. (6.69 kg).

Agency Approvals



UL Listed for Commercial CCTV Equipment
(UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98,
Audio, Video and Similar Equipment.

Enclosure Dimensions (*H x W x D approximate*):
3.26" x 19.125" x 8.5" (83mm x 486mm x 216mm)

