



## **R615DC8ULCB** **DC Rack Mount CCTV Power Supply**

Rev. R615DC8ULCB\_10202014



R615DC8ULCB

### **Overview**

R615DC8ULCB provides 6-15VDC distributed via eight (8) PTC protected outputs for powering CCTV cameras, heaters and other video accessories.

### **Specifications**

#### ***Input:***

- 115VAC, 50/60Hz, 0.9 amp.

#### ***Output:***

- Eight (8) Class 2 Rated PTC protected outputs.
- 6-15VDC @ 4 amp total output current.  
(0.5 amp per device, 2.5 amp max.).
- Outputs are rated @ 2.5 amp.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

#### ***Electrical:***

- Operating temperature: 0° C to 49° C ambient.
- 12.28-30.71 BTU/Hr.
- System AC input VA requirement: 103.5VA.

#### ***Features:***

- Eight (8) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.

#### ***Mechanical:***

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.):  
3.26" x 19.125" x 8.5" (83mm x 486mm x 216mm)
- Product weight (approx.): 12.4 lbs. (6.19 kg).
- Shipping weight (approx.): 13.4 lbs. (6.65 kg).

### **Agency Approvals**



UL Listed for Commercial CCTV Equipment  
(UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98,  
Audio, Video and Similar Equipment.

**Enclosure Dimensions** (*H x W x D approximate*):  
3.26" x 19.125" x 8.5" (83mm x 486mm x 216mm)

