



RBOC7

### Overview

The RBOC7 Open Collector Module incorporates seven (7) open collector outputs capable of sinking 100mA which can be activated via positive (+) low current trigger inputs.

### Specifications

#### **Input Voltage:**

- 12VDC or 24VDC operation.
- Seven (7) independent (3VDC to 24VDC @ 2mA minimum) positive inputs.

#### **Outputs:**

- Seven (7) open collector outputs capable of sinking 100mA each.

#### **Mechanical:**

- Dimensions (W x L x H approx.): 3.25" x 6.5" x 1" (82.55mm x 165.1mm x 25.4mm)
- Product weight (approx.): 0.1 lbs. (0.05 kg).
- Shipping weight (approx.): 0.15 lbs. (0.07 kg).

#### **Board Dimensions** (W x L x H approx.):

3.25" x 6.5" x 1" (82.55mm x 165.1mm x 25.4mm)

