



SMP5CTX

Overview

SMP5CTX power supply/charger converts a 115VAC/230VAC, 50/60Hz input into a regulated 12VDC or 24VDC output @ 4 amp continuous supply current.

Specifications***Input:***

- Input 115VAC, 50/60Hz, 0.95 amp or 230VAC, 50/60Hz, 0.5 amp.

Output:

- 12VDC or 24VDC selectable output.
- 4 amp supply current.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Battery Backup:

- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 0.5 amp.
- Zero voltage drop when switching over to battery backup.

Visual Indicators:

- AC input and DC output LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
 - 12VDC: 24.57 BTU/Hr.
 - 24VDC: 49.13 BTU/Hr.
- System AC input VA requirement:
 - 115VAC: 109.25VA.
 - 230VAC: 115VA.

Mechanical:

- Enclosure Dimensions (H x W x D approx.):
13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)
 - Accommodates up to two (2) 12VDC/7AH batteries.
- Product weight (approx.): 7.4 lbs. (3.36 kg).
- Shipping weight (approx.): 8.3 lbs. (3.76 kg).

Enclosure Dimensions (H x W x D approximate):

13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)

