



# **WPTV248300ULCB** **UL Listed AC Outdoor CCTV Power Supply**

Rev. DSWPTV248300ULCB\_11102014



WPTV248300ULCB

## **Overview**

WPTV248300ULCB outdoor CCTV Power Supply provides power via eight (8) PTC protected Class 2 rated power-limited outputs for CCTV Cameras, heaters, and other video accessories.

## **Specifications**

### **Input:**

- 115VAC, 50/60Hz, 2.7 amp.

### **Output:**

- Eight (8) Class 2 Rated PTC protected power-limited outputs.
- 24VAC @ 12.5 amp (300VA) supply current.
- or 28VAC @ 10 amp (280VA) supply current.
- Outputs are rated @ 2.5 amp.
- Surge suppression.

### **Electrical:**

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.: 153.55 BTU/Hr.
- System AC input VA requirement: 310.5VA.

### **Features:**

- Secondary fuse rated @ 5 amp/250V.
- Unit maintains camera synchronization.
- AC power LED.
- Power ON/OFF switch.
- Spare fuses provided.
- (all models w/primary and/or secondary fuses).
- NEMA 4 Rated enclosure for outdoor use.

### **Mechanical:**

- Enclosure Dimensions (H x W x D approx.): 12" x 8" x 6" (304.8mm x 203.2mm x 152.4mm).
- Product weight (approx.): 14.4 lbs (6.53 kg).
- Shipping weight (approx.): 16.4 lbs (7.44 kg).

## **Agency Approvals**



UL Listed for Commercial CCTV Equipment (UL 2044).



European Conformity



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

## **PMK1 Pole Mount Kit (order separately)**



PMK1

PMK1 pole mount kit is designed to simplify installation of outdoor units.

- Accommodates 2"- 8"(diameter) poles.
- Kit includes:
  - Two (2) powder coated steel mount brackets.
  - Four (4) stainless steel bolts.
  - Four (4) stainless steel lock washers.
  - Two (2) wormgear quick release straps.

**Enclosure Dimensions (H x W x D approximate):**

12" x 8" x 6" (304.8mm x 203.2mm x 152.4mm)

