

16-port and 24-port Gigabit SMB Wired Switching Hubs

Buffalo's BS-G21U unmanaged business-class multiport gigabit switches offer a quick and easy way to extend your office network at fast gigabit Ethernet speeds. Plug and play installation requires no additional software or configuration; simply plug your network ready devices into one of the available Ethernet ports. Each AUTO-MDIX port automatically detects and configures the correct connection while optional jumbo frame support provides maximum performance.

The BS-G21U unmanaged business-class gigabit switches include Intelligent Power Control, an energy conservation feature that monitors the activity status of each port to greatly reduce the total power consumed. The durable metal chassis is rack-mountable and equipped with holes for wall-mounting or rubber feet for easy placement on a desktop. Fast networking speeds, eco minded operation and performance-minded features make Buffalo BS-G21U unmanaged business-class multiport gigabit switches a perfect network extension solution for your office.

GIGABIT ETHERNET

Gigabit Ethernet ports
for fast data transfers

AUTO-MDIX

Detects and configures the
correct connection

INTELLIGENT POWER CONTROL

Automatically adjusts port
power to reduce power
consumption by up to 64%

Features and Benefits

Easily Extend Your Office Network: Integrates any Ethernet enabled device with plug and play setup

High Performance: Connect and upgrade devices and workstations to fast gigabit speeds

Durable Metal Chassis: Fanless, compact design offers silent and reliable operation

Gigabit Ethernet: Multiple gigabit ports for fast transfer rates

Fast and Easy Setup: Auto-MDIX provides fast plug and play setup with any Ethernet cable

Flexible Placement: Easily mount in a rack, on a wall or place on a desktop

Available in 16-port and 24-port configurations



* Power saving is not available for computers configured to use Wake-on-LAN.



BS-G2116U (16-port)



BS-G2124U (24-port)

OS Support

Windows® 7 (32/64-bit)	Windows® 98
Windows Vista® (32/64-bit)	Mac OS® X
Windows® XP	Mac OS® 9
Windows® 2000	Mac OS® 8.6
Windows® Me	

What's in the Box

Unmanaged Gigabit Switch	Magnets (2)
AC Cord	Screws (2)
Rubber feet (4)	Mounting Bracket
Warranty Statement	

Specifications

Standard Compliance	IEEE802.3, IEEE802.3u, IEEE802.3ab, AUTO-MDIX
Number of Ports:	16 (BS-G2116U) 24 (BS-G2124U)
Data Transfer Rates	10/100/1000 Mbps
Transmission Types	(10BASE-T) / 4B5B/MLT-3 (100BASE-TX)/ 4D-PAM5(1000BASE-T)
Connector Type	RJ-45
Weight (oz.)	7.5
Power Consumption	9 W Max (BS-G2116U) 16.5 W Max (BS-G2124U)
Power Supply	AC 100-240 V 50/60 Hz