

EASY TO USE

USB 3.0 DESKTOP HARD DRIVE



Buffalo's DriveStation AxisTM is an easy to use 1-drive storage solution for the easy addition of external storage to any device using a USB port. It features a sleek, attractive chassis that can be positioned vertically or horizontally, adapting to the location it is used in for efficient use of space. With USB 3.0 support and backward compatibility with USB 2.0, DriveStation Axis USB 3.0 works with almost any PC or Mac® computer and provides interface speeds up to 5 Gbps*. Simply plug it in to any USB port and instantly expand storage or schedule automatic backups with USB plug and play connectivity. Additionally, DriveStation Axis has been performance tested for use with Wii U and offers easy, reliable Wii storage.

FEATURES

EASY TO USE STORAGE

With terabytes of storage, DriveStation Axis USB 3.0 provides a reliable, easy to use storage for your PC and Mac® computer. Quickly expand the capacity of your computer for your favorite music, photos, videos and more. The simple USB 2.0 interface offers plug and play setup and universal connectivity.

EASY SCHEDULED BACKUP

DriveStation Axis is perfect for backing up your important files. Disaster and hard drive failures can occur unexpectedly; don't leave your important files and treasured memories in the hands of chance. Schedule regular backups for your PC with Buffalo Backup Utility or use Time Machine for your Mac. Protect all of your data, down to the last byte.




WORKS WITH WII U

Easily expand the storage capacity of your Wii U gaming system to save game data and downloadable software with this Wii U hard drive. DriveStation Axis has been tested to work with Wii U, offering compatible, reliable Wii U storage.

UNIQUE FORM FITS ANYWHERE

DriveStation Axis features a sleek, attractive chassis that can be positioned vertically or horizontally, adapting to the location it is used in for efficient use of space. Stand it upright on your home office desktop or lay it flat below your TV as part of your media center.

MEDIA STORAGE CAPACITY

HDD Size↓	 Photos*	 Movies†	 Songs‡
1 TB	450,000	1,000	250,000
2 TB	900,000	2,000	500,000
3 TB	1,350,000	3,000	750,000
4 TB	1,800,000	4,000	1,000,000

Results will vary based on individual factors.

** Figures represent the average number of photos taken with a 10 megapixel camera with an average file size of 2.2 MB per photo.*

† Figures represent the number of movies based on an average file size of 1 GB per movie.

‡ Figures represent the number of MP3 files at an average length of 00:03:25/160 Kbps with an average file size of 4 MB per song.

1 MB = 1,000,000 bytes, 1 GB = 1,000,000,000 bytes, 1 TB = 1,000,000,000,000 bytes. Total accessible capacity varies depending on operating environment.

BUFFALO TOOLS

Buffalo Tools is a feature-rich suite of optional software included on many Buffalo DriveStation and MiniStation storage products. Any or all of the following components of Buffalo Tools may be installed on Windows PCs.

- Buffalo's Backup Utility for Windows PCs and can be used to back up one or multiple computers with a single Buffalo external hard drive.

- eco Manager is an energy efficiency tool used to conserve energy and reduce battery consumption.

- RAMDISK is a simple utility that allows you to create a RAM disk on your Windows PC.

- SecureLock for Windows® provides complete control of the data encryption on your Buffalo external hard drive, providing password protection and software data encryption.

Adaptable Positioning



Lay flat or stand upright for placement just about anywhere!

MODELS

HD-LB1.0TU3, HD-LB2.0TU3, HD-LBU3.0TU3
HD-LB4.0TU3

BOX CONTENTS

DriveStation Axis HD-LBU3, Quick-Setup Guide,
AC Adapter, Warranty Statement

SPECIFICATIONS

INTERNAL HARD DRIVES

Number of Drives	1
Drive Interface	SATA 3 Gbps
Hard Drive Sizes:	1 TB, 2 TB, 3 TB, 4 TB
Total Hard Drive:	1 TB, 2 TB, 3 TB, 4 TB

USB INTERFACE

Standard Compliance	USB 3.0 / 2.0
Connector Type	Type A
Number of Ports	1
Data Transfer Rate	Max: 5 Gbps (USB 3.0) Max 480 Mbps (USB 2.0)

OTHER

Dimensions (W x H x D in)	1.5 x 4.8 x 7.5
Weight (lbs)	2.1
Operating Environment	41-95°
Power Consumption (Watts)	Max. 18 W
Power Supply	AC 100-240V 50/60 Hz
Client OS Support	Windows® 8 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit/64-bit), Windows® XP, Mac OS® X 10.5 - 10.8**

** The HDD default format is NTFS; to work with Mac, reformat the HDD using Mac Disk Utility. Only basic external hard drive functionality is supported with this operating system; some included utilities may not work.

24/7 TECH SUPPORT | 1 YEAR WARRANTY

(866) 752-6210 | USA & Canada Only

*Only basic external hard drive functionality is supported in these operating systems, some included utilities may not work.

1 TB = 1,000,000,000,000 bytes; total accessible capacity varies depending on operating environment. Data rate, features and performance may vary based on the configuration of your system and other factors. Buffalo Technology (Buffalo Inc.) shall not be responsible for data loss and shall have no liability arising out of damages from lost data.

©2013 BUFFALO INC. All rights reserved. BUFFALO and BUFFALO logo are either trademarks or registered trademarks of MELCO HOLDINGS INC. DriveStation and DriveStation logo are either trademarks or registered trademarks of BUFFALO INC. or its affiliates in the United States and other countries. The names and logos of other companies mentioned herein belong to their respective owners.