

5-port and 8-port Gigabit Wired Switching Hubs

Buffalo's Multiport Gigabit Wired Switch offers a quick and easy way to extend your home or small office network with fast gigabit Ethernet speeds. Plug and play installation requires no additional software or configuration; simply plug in your network ready devices to one of the available gigabit Ethernet ports. Each AUTO-MDIX port automatically detects and configures the correct connection while optional jumbo frame support provides maximum performance.

The Buffalo Gigabit Wired Switch includes Intelligent Power Control, an energy conservation feature that monitors the activity status of each port to reduce the total power consumed by up to 68%. The light and durable chassis is equipped with holes for wall-mounting or rubber feet for easy placement on a desktop. Fast networking speeds, eco minded operation and performance minded features make the Buffalo Multiport Gigabit Wired Switch a perfect network extension solution for your home or small office.

GIGABIT ETHERNET

Gigabit Ethernet ports
for fast data transfers

SIMPLE SETUP

Plug and Play
for a hassle free setup

INTELLIGENT POWER CONTROL

Automatically adjusts port
power to reduce power
consumption by up to 68%

Features and Benefits

Use with any Ethernet enabled device: PCs, TVs, gaming consoles and other digital home appliances

Intelligent Power Control: Power supplied to ports is automatically monitored and controlled for energy savings up to 68%*

Gigabit Ethernet: Five gigabit ports for fast transfer rates

Loop Detection: Minimizes the impact of network disruptions

Plug and Play: Just plug in your Ethernet cables and connect to power

Compact and Lightweight: Durable, lightweight case for placement anywhere

Available in 5-port and 8-port configurations



* Power saving is not available for computers configured to use Wake-on-LAN.



LSW3-GT-5EP/W (5-port)



LSW4-GT-8EP/W (8-port)

OS Support

Windows® 7 (32/64-bit)
Windows Vista® (32/64-bit)
Windows® XP
Mac OS® X
Mac OS® 9
Mac OS® 8.6

What's in the Box

Gigabit Wired Switch
Warranty statement
AC Adapter
Rubber feet (4)
Magnets (2)
Screws (2)

Specifications

| | |
|----------------------------|--------------------------------------------------------------------------|
| Standard Compliance | IEEE802.3, IEEE802.3u, IEEE802.3ab, IEEE802.3x (Flow Control), AUTO-MDIX |
| Number of Ports: | 5 (LSW3-GT-5EP/W) 8 (LSW4-GT-8EP/W) |
| Data Transfer Rates | 10/100/1000 Mbps |
| Transmission Types | (10BASE-T) / 4B5B/MLT-3 (100BASE-TX) / 4D-PAM5(1000BASE-T) |
| Connector Type | RJ-45 |
| Dimensions (W x H x D in.) | 4.5 x 1.3 x 3.9 |
| Weight (oz.) | 7.5 |
| Power Consumption | 3.8 W Max (LSW3-GT-5EP/W) 5.06 W Max (LSW4-GT-8EP/W) |
| Power Supply | AC 100-240 V 50/60 Hz |