

## HIGH PERFORMANCE

### 2-DRIVE NETWORK STORAGE



LinkStation™ Pro Duo offers instant storage expansion and file access on your home or home office network and over the Internet. Twice as fast as a standard NAS, LinkStation Pro Duo features a high-speed, 1.6 GHz processor for maximum transfer speeds up to 72 MBps. Plug it into any network Ethernet port or into the back of your wireless router and access it on any networked device in your house. Equipped with LinkStation Pro Duo is a built-in BitTorrent™ client, a DLNA Certified™ media server and an iTunes® server for effort-free downloading and streaming your favorite movies, photos, music and more.

LinkStation Pro Duo is also available as a diskless enclosure LS-WVL/E, allowing you to select your own hard drives for a customizable, scalable storage solution.

## FEATURES

### SECURE CENTRAL STORAGE

With terabytes of storage, LinkStation Pro Duo provides a reliable, central location to store and protect all data from every PC and Mac® computer, tablet device and smartphone in your home or small office. Store, access and share files from anywhere over your wireless network at speeds up to twice as fast as a standard USB hard drive.

### EXCEPTIONAL PERFORMANCE

Equipped with a high performance 1.6 GHz processor and DDR3 RAM, LinkStation Pro Duo offers much more than simple home shared storage. This single drive network storage device boasts transfer speeds up to 72 MB/s, nearly twice as fast as a standard USB drive.

### STREAM YOUR FAVORITE MEDIA

LinkStation Pro Duo is DLNA Certified, supports Squeezebox and can be used as an iTunes server to stream all of your favorite music, movies and shows to multiple devices simultaneously. Now you can relax and watch movies on your big screen TV while music is pumped outdoors by the pool.

### EASY SCHEDULED BACKUP

LinkStation Pro Duo features NovaBACKUP® Professional for Windows® and Time Machine® support for Mac for whole home data backup. Disaster and hard drive failures happen unexpectedly; don't leave your important files and treasured memories in the hands of chance. Schedule backups for every computer in your house and easily protect all of your data, down to the very last byte.

### MEDIA STORAGE CAPACITY

HDD Size↓	Photos*	Movies†	Songs‡
1 TB	450,000	1,000	250,000
2 TB	900,000	2,000	500,000
4 TB	1,800,000	4,000	1,000,000
6 TB	2,700,000	6,000	1,500,000

Results will vary based on individual factors.

\* Figures represent the average number of photos taken with a 10 megapixel camera with an average file size of 2.2 MB per photo.

† Figures represent the number of movies based on an average file size of 1 GB per movie.

‡ Figures represent the number of MP3 files at an average length of 00:03:25/160 Kbps with an average file size of 4 MB per song.

1 MB = 1,000,000 bytes, 1 GB = 1,000,000,000 bytes, 1 TB = 1,000,000,000,000 bytes. Total accessible capacity varies depending on operating environment.

### AUTOMATIC DATA PROTECTION

LinkStation Pro Duo features two hard drives\* and support for RAID 0/1 for maximum capacity or redundant data protection.

- RAID 0 combines all drives into a single array offering maximum capacity with no redundancy
- RAID 1 automatically creates an exact copy of your data on the second hard drive

### FREE PERSONAL CLOUD SERVICE

Buffalo's free WebAccess service allows you to create a personal cloud for easy remote access and file sharing with anyone, anywhere over the Internet. Your data remains securely stored in one place on your home network, but you can access it quickly from any computer, tablet or smartphone device over the Web.

For enhanced access on the go, download Buffalo's free WebAccess mobile apps for Apple®, Android™ and Windows.



## LINKSTATION NAS SYSTEM

LinkStation<sup>TM</sup> Pro Duo runs on Buffalo's LinkStation NAS System, providing a host of useful features from network file sharing and security to RAID management, remote access and more. Included on all Buffalo LinkStation devices, LinkStation NAS System simplifies your everyday data needs.

## MODELS

LS-WV2.0TL/R1, LS-WV4.0TL/R1, LS-WV6.0TL/R1, LS-WVL/E

## BOX CONTENTS

LinkStation Pro Duo LS-WVL, Setup CD-ROM, Quick-Setup Guide, Ethernet Cable, AC Adapter, Warranty Statement

## SPECIFICATIONS

### INTERNAL HARD DRIVES

Number of Drives*	2
Drive Interface	SATA 3 Gbp/s
Hard Drive Sizes	1 TB, 2 TB, 3 TB
Hard Drive Capacities	2 TB, 4 TB, 6 TB
Supported RAID Levels	0, 1, Normal

### LAN INTERFACE

Standard Compliance	IEEE802.3ab / IEEE802.3 / IEEE802.3u Standard
Data Transfer Rates	10 / 100 / 1000 Mbps
Connector Type	RJ 45
Number of Ports	1

### USB INTERFACE

Standard Compliance	USB 2.0
Connector Type	USB Type A
Number of Ports	1
Data Transfer Rate	Max: 480 Mbps

### PROTOCOL SUPPORT

Networking	TCP/IP
File Sharing	CIFS/SMB, FTP, HTTP/HTTPS, AFP
Management	HTTP/HTTPS
Time Synchronization	NTP

### 24/7 TECH SUPPORT | 1 YEAR WARRANTY

(866) 752-6210 | USA & Canada Only

\*LS-WVL/E does not include hard drives. It is a 2-bay diskless enclosure.

1 TB = 1,000,000,000,000 bytes; total accessible capacity varies depending on operating environment. Data rate, features and performance may vary based on the configuration of your system and other factors. Buffalo Technology (Buffalo Inc.) shall not be responsible for data loss and shall have no liability arising out of damages from lost data.

### OTHER

Dimensions (W x H x D in)	8.1 x 5.1 x 3.4
Weight (lbs)	5.1 lbs, 1.76 lbs (LS-WVL/E)
Power Consumption (Watts)	Max 48 W
Power Supply	AC 100-240V 50/60 Hz
Client OS Support	Windows <sup>®</sup> 8 (32-bit/64-bit), Windows <sup>®</sup> 8.1 (32-bit/64-bit), Windows <sup>®</sup> 7 (32-bit/64-bit), Windows Vista <sup>®</sup> (32-bit/64-bit), Windows <sup>®</sup> XP, Windows <sup>®</sup> 2000, Windows Server <sup>®</sup> 2003, Windows Server <sup>®</sup> 2008 R2, WIndows Server <sup>®</sup> 2003, Mac OS <sup>®</sup> X 10.5 - 10.9



LinkStation Pro Duo is also available as a diskless enclosure LS-WVL/E, allowing you to select your own hard drives for a customizable, scalable storage solution.