



DD-WRT OPEN SOURCE



AirStation™ N300 Open Source DD-WRT Wireless Router is a high speed, open source wireless solution, delivering high speed 11n networking. Ideal for high bandwidth applications, it features an 600 MHz processor and is equipped with onboard amplifiers to provide maximum radio power for improved performance and range. Open source DD-WRT offers advanced features and low-level device management, unlocking extensive capabilities and potential with increased network stability.

FEATURES

OPEN SOURCE DD-WRT ROUTER


AirStation N300 DD-WRT is powered by the leading open-source firmware, equipped with robust and high performance features for custom configuration to optimize performance, security and routing options. Advanced features also include VPN endpoints, hotspot sign in, VLAN and more.

- PPTP and OpenVPN servers
- VPN passthrough
- Advanced QoS controls for bandwidth allocation
- WDS wireless bridging/repeating
- DNS caching
- Viewable performance statistics to measure bandwidth levels
- Set up as a Wi-Fi hotspot
- RADIUS authentication for additional wireless security
- VLAN support
- DHCP server
- Create multiple SSIDs
- NAT support
- Telnet and SSH Root access





dd-wrt.com
for **BUFFALO**TM



2.4 GHz Speeds up to
300 Mbps!

SPECIFICATIONS

WIRELESS LAN INTERFACE

Standard Compliance:	IEEE802.11n/g/b
Frequency Range:	2.4 GHz
Wireless Security:	WPA2-PSK (AES), WPA-PSK (AES), WPA/WPA2-mixed (AES/TKIP), 128/64-bit WEP

WIRED LAN INTERFACE

Standard Compliance:	IEEE802.3/3u/3ab
Speed and Flow Control:	10/100 Mbps (Auto Sensing)
Number of LAN Ports:	4 Ports (RJ-45 Auto MDIX)
Number of WAN Ports:	1 Ports (RJ-45 Auto MDIX)

OTHER

Dimensions (W x H x D):	2.16 x 6.26 x 5.13 in
Weight:	0.59 lbs
Operating Environment:	32-104°F (0-40°C), 10-85% (non-condensing)
Power Supply:	External AC 100-240V Universal, 50/60 Hz
Power Consumption:	10.2W (Maximum)
OS Support:	Windows® 8 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit/64-bit), Windows® XP, Mac OS® X 10.5-10.8

BOX CONTENTS

AirStation N300 Open Source DD-WRT Router, Quick Setup Guide,
Setup Card, Ethernet Cable, AC Adapter, Stand, Wall Screws, Warranty
Statement

24/7 TECH SUPPORT | 3 YEAR WARRANTY

(866) 752-6210 | USA & Canada Only

*300 Mbps is the maximum aggregate wireless signal rate derived from IEEE 802.11n standard specifications achievable using two streams of 150 Mbps each. Actual data throughput and range will vary depending upon network conditions and environmental factors, including volume of network traffic, building materials and construction and network overhead. Maximum speed and range is achievable when used with same enhanced mode technology.

©2014 BUFFALO INC. All rights reserved. BUFFALO and BUFFALO logo are either trademarks or registered trademarks of MELCO HOLDINGS INC. AirStation is either a trademark or registered trademark of BUFFALO INC. Microsoft Windows, Windows Vista and Windows logo are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Mac OS is a trademark of Apple Inc., registered in the U.S. and other countries. The names and logos of other companies mentioned herein belong to their respective owners.