



HIGH PERFORMANCE

HIGHPOWER N600 GIGABIT DUAL BAND WIRELESS ROUTER

Buffalo's AirStation HighPower N600 Gigabit Dual Band Wireless Router WZR-600DHP is a versatile dual band solution, ideal for the home and small office environments. With five gigabit Ethernet ports and simultaneous wireless operation on both 2.4 GHz and 5 GHz bands, the WZR-600DHP is perfect for streaming HD movies, music and emailing from multiple devices at the same time. Coupled with HighPower technology, the WZR-600DHP provides exceptional range and increased performance at range for a better connection anywhere on your home network. Multi-level wireless encryption options and an easy-to-use step-by-step setup wizard that guides you through configuration from start to finish allows you to set up a secure, high performance wireless network within minutes of opening the box. Plus, you can use the USB Share Port to connect a USB hard drive for easy file sharing, media streaming and central storage or to add a printer to your home network.

FEATURES

DUAL BAND

Offering simultaneous wireless operation on both the 2.4 GHz and 5 GHz bands, the AirStation HighPower N600 Gigabit Dual Band Wireless Router is perfect for streaming HD movies, music and emailing from multiple devices at the same time.

Dual Band N600: Concurrent high speed wireless connections with up to 300 Mbps on single band and up to 600 Mbps on both bands.

OPEN SOURCE DD-WRT ROUTER

AirStation HighPower N600 Gigabit Dual Band Wireless Router is powered by the leading open-source firmware, equipped with robust and high-performance features for custom configuration. Intuitive interface helps you set up and connect in no time

Customizable advanced features allow to optimize wireless performance, security and routing options

Advanced features also include VPN endpoints, hot-spot sign in, VLAN and more.

MAXIMUM WIRELESS COVERAGE

Dead spots in your home or office can slow down your wireless access and even prevent you from getting online. Advanced HighPower technology from Buffalo enhances signal strength and can almost double the range.

- Stay connected from anywhere in your home or office
- Connect with confidence every time

FAST WIRELESS CONNECTIVITY

With speeds up to 600 Mbps, AirStation HighPower N600 Gigabit Dual Band Wireless Router provides a fast wireless connection perfect for surfing and emailing from multiple computers, downloading files and streaming music, movies and other multimedia content from the Web. Easily connect with your computer, tablet and smartphone devices.

GIGABIT ETHERNET

Maximize your wireless network speed with gigabit Ethernet connections that keep your data moving at lightning speed.

COMPATIBILITY

Easily upgrade to your network from the old Wireless-G standard and maintain compatibility with existing adapters and devices. AirStation HighPower N600 Gigabit Dual Band Wireless Router works with any new Wireless-N device as well as the previous generation Wireless-G.

EASY SETUP

AirStation HighPower N600 Gigabit Dual Band Wireless Router features an easy to use step by step setup wizard that guides you through configuration from start to finish. Within moments of opening the box you will have a secure wireless home network.

WIRELESS SECURITY

AirStation HighPower N600 Gigabit Dual Band Wireless Router features multi-level wireless encryption options to prevent unauthorized access and protect your important data.





USB PORT FOR NETWORK SHARING

Connect a USB drive for easy file sharing and media streaming or add a printer to your home network.

- Store files in one central location
- DLNA Certified® for easy media streaming
- Connect a network printer

SPECIFICATIONS

WIRELESS LAN INTERFACE

Standard Compliance:	IEEE802.11n, IEEE802.11a, IEEE802.11g, IEEE802.11b
Frequency Range:	Concurrent dual band 2.4GHz / 5 GHz Support
Access Mode:	Infrastructure Mode
Antenna (Tx x Rx):	2 x 2
Wireless Security:	WPA - PSK (AES, TKIP), WPA2-PSK (AES, TKIP), 128/64-bit WEP

WIRED LAN INTERFACE

Speed and Flow Control:	10/100/1000 Mbps, Auto Sensing, Auto MDIX
Number of LAN Ports:	4 x RJ-45
Number of WAN Ports:	1 x RJ-45
WAN Port Security:	VPN Pass Through, SPI, Dynamic Packet Filtering

USB Interface

Standard Compliance:	USB 2.0
Connector Type:	A type
Number of Ports:	1

OTHER

Dimensions (W x H x D)	6.2 x 6.5 x 1.4 in
Weight	0.73 lbs
Power Consumption	Max 13.2 W
Power Supply:	External AC 100-240V input, 12V DC Output
OS Compatibility:	Windows® 8 (32/64-bit), Windows® 7 (32/64-bit), Windows Vista® (32/64-bit), Windows® XP, Mac OS® X 10.4-10.7**

BOX CONTENTS

AirStation HighPower N600 Gigabit Dual Band Wireless Router
Quick Setup Guide
Setup CD-ROM
Setup Card
Ethernet Cable
AC Adapter
Stand
Screws for Wall Mounting
Warranty Statement

5 GHz Speeds up to
300 Mbps!
2.4 GHz Speeds up to
300 Mbps!



Stream your favorite music and HD video, and game online, interference free!



24/7 TECH SUPPORT | 3 YEAR WARRANTY
(866) 752-6210 | USA & Canada Only

**AOSS support requires use of Buffalo Client Manager software which is only compatible with Windows® systems. Some initial setup utilities only work with Windows systems.

*600 Mbps is the maximum aggregate wireless signal rate derived from IEEE 802.11n standard specifications achievable using two streams of 150 Mbps each on two concurrent bands. Actual data throughput and range will vary depending upon network conditions and environmental factors, including volume of network traffic, building materials and construction and network overhead. Maximum speed and range is achievable when used with same enhanced mode technology.

©2013 BUFFALO INC. All rights reserved. BUFFALO and BUFFALO logo are either trademarks or registered trademarks of MELCO HOLDINGS INC. AirStation and AirStation logo are either trademarks or registered trademarks of BUFFALO INC. The names and logos of other companies mentioned herein belong to their respective owners.