



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS25010
 781810232965
 250-10 1-SIDED-10 UNITAP
 Active

Web Use
 BURNDY Product Line

Width (in) 2.07
 Hex Size (Key) 5/16
 Length (in) 9.53
 Height (in) 2.13

Dimensional

Min Voltage Rating 600

Electrical

Number of Ports 10
 Number of Screws 10

General

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 10
 Port, 1 Sided Entry, 10 AWG-250
 kcmil, Al/Cu Rated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

8 AWG-250 kcmil
 N/A
 10 AWG-250 kcmil

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical

Aluminum
 Unplated
 Plastisol
 N
 Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175