



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS45
781810223833
14-4 ONE SIDED UNITAP
Active

Web Use
BURNDY Product Line

Screw Size
Width (in)
Hex Size (Key)
Length (in)
Height (in)

Min Voltage Rating

Number of Ports
Number of Screws

Product Description

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

Type of Hardware
Type of Plating
Insulation Type
Plated (Yes or No)
Product Material

UL Listed
CSA Certified
Rated for Direct Burial
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Documentation

Dimensional

1/4
1.25
1/8
2.39
1.25

Electrical

600

General

5
5
Aluminum Multiple Tap
Connector, Clear Insulated, 5 Port,
1 Sided Entry, 14-4 AWG, Al/Cu
Rated

Conductor(s)

8 AWG-4 AWG
N/A
14 AWG-4 AWG

Physical

Aluminum
Unplated
Plastisol
N
Aluminum

Approvals / Certifications

Y
Y
N
Compliant
N
N
UL468A-468B

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175