



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

BIBS46
781810223840
14-4 ONE SIDED UNITAP
Active

Web Use
BURNDY Product Line

	Dimensional
Screw Size	1/4
Width (in)	1.25
Hex Size (Key)	1/8
Length (in)	2.83
Height (in)	1.25
	Electrical
Min Voltage Rating	600
	General
Number of Ports	6
Number of Screws	6
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 6 Port, 1 Sided Entry, 14-4 AWG, Al/Cu Rated
	Conductor(s)
Aluminum Size (Range)	8 AWG-4 AWG
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14 AWG-4 AWG
	Physical
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
	Approvals / Certifications
UL Listed	Y
CSA Certified	Y
Rated for Direct Burial	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175