



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS48
 781810225288
 14-4 ONE SIDED UNITAP
 Active

Web Use
 BURNDY Product Line

Screw Size 1/4
 Width (in) 1.25
 Hex Size (Key) 1/8
 Length (in) 3.71
 Height (in) 1.25

Dimensional

Min Voltage Rating

600

Number of Ports
 Number of Screws

8

8

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 8 Port,
 1 Sided Entry, 14-4 AWG, Al/Cu
 Rated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

8 AWG-4 AWG

N/A

14 AWG-4 AWG

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical

Aluminum

Unplated

Plastisol

N

Aluminum

Approvals / Certifications

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y

Y

N

Compliant

N

N

UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175