



[On Line Catalog](#)



BURNDY Catalog Number	BIBS60010
UPC Number	781810233030
Description	600-4 1-SIDED-10 UNITAP
Status	Active
Web Use	
BURNDY Product Line	
Dimensional	
Width (in)	2.38
Hex Size (Key)	3/8
Length (in)	12.97
Height (in)	2.75
Electrical	
Min Voltage Rating	600
General	
Number of Ports	10
Number of Screws	10
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 10 Port, 1 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated
Conductor(s)	
Aluminum Size (Range)	4 AWG-600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4 AWG-600 kcmil
Physical	
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA	BURNDY Technical Servcies	Hours: 8.00 AM - 5.00 PM
47, industrial Park Drive	47, industrial Park Drive	Monday - Friday
Manchester NH03109	Manchester NH03109	Phone: 000-346-4175