



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS6003
 781810224106
 600-4 ONE SIDED UNITAP
 Active

Web Use
 BURNDY Product Line

Width (in) 2.38
 Hex Size (Key) 3/8
 Length (in) 4.00
 Height (in) 2.75

Dimensional

Min Voltage Rating 600

Electrical

Number of Ports 3
 Number of Screws 3

General

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 3 Port,
 1 Sided Entry, 4 AWG-600 kcmil,
 Al/Cu Rated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

4 AWG-600 kcmil
 N/A
 4 AWG-600 kcmil

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical

Aluminum
 Unplated
 Plastisol
 N
 Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175