



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS6006
 781810224137
 600-4 ONE SIDED UNITAP
 Active

Web Use
 BURNDY Product Line

Width (in)
 Hex Size (Key)
 Length (in)
 Height (in)

Dimensional

2.38
 3/8
 7.84
 2.75

Min Voltage Rating

Electrical

600

Number of Ports
 Number of Screws

General

6
 6

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 6 Port,
 1 Sided Entry, 4 AWG-600 kcmil,
 Al/Cu Rated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

4 AWG-600 kcmil
 N/A
 4 AWG-600 kcmil

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical

Aluminum
 Unplated
 Plastisol
 N
 Aluminum

Approvals / Certifications

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

N
 Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday

Phone: 000-346-4175