



On Line Catalog



BURNDY Catalog Number	BIBS75014
UPC Number	781810233122
Description	750-2 1-SIDED-14 UNITAP
Status	Active
Web Use	
BURNDY Product Line	
	Dimensional
Width (in)	2.70
Hex Size (Key)	3/8
Length (in)	19.13
Height (in)	3.00
	Electrical
Min Voltage Rating	600
	General
Number of Ports	14
Number of Screws	14
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 14 Port, 1 Sided Entry, 2 AWG-750 kcmil, Al/Cu Rated
	Conductor(s)
Aluminum Size (Range)	2 AWG-750 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-750 kcmil
	Physical
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
	Approvals / Certifications
Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175